

Confidea Wireless G3



televic
conference

The most **RELIABLE** & **FLEXIBLE** WIRELESS CONFERENCE SYSTEM



The 3rd and newest generation of Televic's renowned Confidea Wireless Conference system uses the latest advances in wireless technologies to offer more stability, more flexibility and more security. All including the globally recognized superior sound quality.

Confidea Wireless G3 is so flexible, so easy to set up and so convenient to use that it is ideal for rental applications, town councils, boardrooms, hotels and universities. A system is set up and torn down in only a few minutes. It is therefore great for temporary set-ups or for multi-purpose rooms.

Basic systems should require basic investment. In its simplest form, a Confidea system requires very few hardware and software components. For a basic discussion system the Confidea Wireless Conference Access Point (WCAP) acts as a mini central unit. The provided audio in- and outputs make it easy to connect a handheld (wireless) microphone, a room audio system, a video conferencing system or a telephone hybrid system.

The new access point has a powerful built-in webserver, so that you are in full control of the system from any desktop computer, laptop, tablet or smartphone. For simple discussion applications, the intuitive user interface offers all functionality you need as an operator, ready to use without specialized software training. A set-up with voting is managed through the CoCon Control Software and the voting units even offer RFID authentication.

The AES encryption, combined with the proprietary communication protocol and access control, offers 3 layers of security and confidentiality at a level not seen in any product of this class. Your sensitive meetings are secure and your IT people reassured of a perfect coexistence of the system with your wireless LAN.

- 1 3 High frequency antennas
- 2 LAN connection
- 3 Balanced Audio OUT
- 4 Balanced Audio IN
- 5 Future extension ports
- 6 Power
- 7 Built-in web control

- 8 Removable gooseneck microphone
- 9 Microphone button
- 10 Priority button (Chairman)
- 11 Next-in-Line button (Chairman)
- 12 Voting buttons
- 13 Start/Pause/Stop voting (Chairman)
- 14 Voting result OLED display
- 15 Headphones volume adjustment
- 16 Broadband loudspeaker
- 17 Headphone connectors
- 18 RFID card reader
- 19 RFID card



ADVANCED

RF Spectrum Management

STATE-OF-THE-ART QUAD BAND WIRELESS SOLUTION

The Confidea wireless conference system uses the 2.4 and 5 GHz frequency range, providing a large number of channels in 4 different bands that guarantee a reliable wireless link at any time.

BUILT-IN SPECTRUM SCANNER


The access point has a built-in spectrum scanner that continuously monitors the 4 bands to detect interference sources and identify free frequencies.

This way, the access point is able to automatically switch - glitch-free - to a 'clean' frequency for a reliable RF link.


MULTI-ROOM CAPABILITY

The multitude of possible operating frequencies and the advanced spectrum management make the Confidea system the ideal solution for buildings where multiple systems are operational in adjacent rooms.

Traditional "Single band" system



Televic Confidea "Quad-band" system



Convenient, Built-in Web Control

Set-up and control from desktop and mobile devices




The Confidea Wireless Conference Access Point (WCAP) has built-in web control that can be accessed from any PC, laptop, tablet or smartphone using a standard (mobile) internet browser.

The built-in web pages allow for set up of the system, but also control and monitoring during the meeting. From the web interface, microphones can be activated or switched off. Also the battery condition of each unit can be checked and monitored without disturbing the ongoing meeting.

The possibilities of the web interface are extensive. For basic discussion systems, this eliminates the need for specialized, dedicated software and software training.

Easy set-up, Operational in Minutes



- 1 Confidea Wireless Access Point
- 2 Confidea Wireless Delegate/Chairman units
- 3 Handheld microphone (optional)
- 4 Laptop or desktop computer
(web browser / CoCon Control Software)
- 5 Android, iOS or Windows tablet
- 6 Smartphone

- 7 (Wireless) Router
- 8 LAN
- 9 Room audio amplifier (optional)
- 10 Room audio speakers (optional)

Battery Management - Simplified

Know the condition of your batteries at all times



ALWAYS FEEL CONFIDENT

The charge indicator on the battery instantly reveals the condition of the battery, even before the system is switched on and operational. It eliminates any doubt about the condition of batteries before the start of the meeting. A fully charged battery will give you 28 hours of operation.

SAVE CHARGING TIME

The Confidea Charging Tray is rack mountable and quickly charges 6 battery packs simultaneously in only 2,5 hours.

Multiple chargers can be daisy-chained via a power loop-through to create a bulk charging station.



Minimum set-up - Maximum flexibility

DISCUSSION

Confidea DD/CD G3

Delegate/Chairman Unit



- Delegate unit for basic discussion
- Screw-lock socket for removable microphone
- Microphone button
- Two headphones connections with single volume control

Chairman unit:

- Priority and 'next' button

VOTING

Confidea DV/CV G3

Delegate/Chairman Unit



- For discussion and electronic voting
- Screw-lock socket for removable microphone
- Microphone button
- Three voting buttons
- 2 OLED information displays
- Two headphones connections with single volume control
- RFID card reader

Chairman unit:

- Priority and 'next' button
- System volume control
- Start and stop voting from the unit
(CoCon Management Software required)

Confidea WCAP G3

Wireless Conference Access Point



- Power Connector
- RJ45 LAN Connection
- 6.3 mm jack balanced analog IN
- 6.3 mm jack balanced analog OUT
- 3 R-SMA antennas
- Built-in web control

Confidea BP

Battery Pack




- Battery condition LED bar
- 'Charging' LED indicator
- Push-to-Test button
- Battery status LED
- Quick release clip
- Autonomy: 28 Hours

Recommended Accessories

D-MICxxSL

Removable design microphone



- Elegant design
- Natural sound
- Immune to mobile interference
- Screw-lock connector
- Different lengths:
30 - 40 - 50 cm
- LED ring (Red = on, Green = Request)

TEL152

Delegate Headphone



- Excellent intelligibility and speech reproduction
- Ultra-lightweight
- Adjustable headband
- Swiveling ear pads
- Comfortable wear
- Replaceable soft ear pads (*optional*)
- Replaceable hard ear pads (*optional*)
- Stereo 3.5 mm angled jack

Confidea CHC

Transport Case



- Pre-formed foam inlays for maximum protection of up to 12 units, 12 microphones and 1 WCAP
- Ready to accept 2 x Confidea CHC charging trays
- Loop-through mains connector
- Extractable handle
- High-quality wheels

Confidea CHT

Rack mountable charging tray



- 19" Rack mountable
- Charges up to 6 batteries
- Loop-through mains connector
- Time to full charge: 2,5 Hours

televic

conference

www.televic-conference.com

Televic - Conference NV (main office)
Leo Bekaertlaan 1
B-8870 IZEGEM
BELGIUM
T. +32 (0)51 303045
F. +32 (0)51 310670

